



UP10-H

10 mm Ø, 0.1 mW - 2 W - Fast & Low Power Thermopile



KEY FEATURES

- 1. **LOW POWER THERMOPILE**
Noise level of a photo detector with the large bandwidth and high power capacity of a thermal device
- 2. **HIGH PERFORMANCE**
Fast Rise Time (1.4 sec)
High Damage Threshold (36 kW/cm²)
- 3. **COMPACT DESIGN**
Only 13 mm thick (UP10P model)
- 4. **IR FILTER (UPF10 MODELS)**
Removes unwanted IR interference
- 5. **ENERGY MODE**
Measure single shot energy up to 3 J
- 6. **SMART INTERFACE**
Containing all the calibration data
- 7. **integra OPTIONS**
 - Standard: USB Output (-INT)
 - In Option: RS-232 Output (-IDR)

AVAILABLE MODELS



UP10P-2S-H5-L



UPF10P-2S-H5-L



UP10K-2S-H5-L



UPF10K-2S-H5-L

ACCESSORIES



Stand with Steel Post
(Model Number: 200160)



Extension Cables
(4, 15, 20 or 25 m)



IR Filter
(Mounted)



Isolation Tube
(Model Number: 202376)



Fiber Adaptors & Connectors
(FC, ST and SMA)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	14
CALIBRATION	6
TECHNICAL DRAWINGS	96
ABSORPTION CURVES	100
COMPATIBLE MONITORS	
MAESTRO	20
TUNER	24
UNO	26
S-LINK	28
P-LINK	30
M-LINK	32
LIST OF ALL ACCESSORIES	194
APPLICATION NOTE	
MEASURING LASER POWER WITH A THERMOPILE DETECTOR: THE BASICS!	202175

MONITORS

ENERGY DETECTORS

POWER DETECTORS

HIGH POWER SOLUTIONS

PHOTO DETECTORS

THZ DETECTORS

OEM DETECTORS

SPECIAL PRODUCTS

BEAM DIAGNOSTICS

UP10-H

CE NIST* Traceable
*Also traceable to NRC-CNRC

SPECIFICATIONS

	UP10P-2S-H5-L	UPF10P-2S-H5-L	UP10K-2S-H5-L	UPF10K-2S-H5-L
MAX AVERAGE POWER	2 W			
EFFECTIVE APERTURE	10 mm Ø			
COOLING METHOD	Convection			
MEASUREMENT CAPABILITY				
Spectral Range *	0.19 – 20 µm	0.28 - 2.1 µm	0.19 – 20 µm	0.28 - 2.1 µm
Noise Equivalent Power ^a	100 µW without anticipation / 30 µW with anticipation and 2 sec moving average			
Rise Time (nominal) ^b	1.4 sec	1.4 sec	1.1 sec	1.1 sec
Sensitivity (typ into 100 kΩ load) ^c	2 mV/W			
Calibration Uncertainty ^d	±2.5 %			
Repeatability	±0.5 %			
Energy Mode				
Sensitivity	2.4 mV/J			
Maximum Measurable Energy ^a	3 J			
Noise Equivalent Energy ^a	5 mJ			
Minimum Repetition Period	2 sec			
Maximum Pulse Width	63 ms			
Accuracy with energy calibration option	±5 %			
DAMAGE THRESHOLDS				
Maximum Average Power Density ^f	36 kW/cm²			
Pulsed Laser Damage Thresholds	Max Energy Density		Peak Power Density	
1064 nm, 360 µs, 5 Hz	5 J/cm²		14 kW/cm²	
1064 nm, 7 ns, 10 Hz	1 J/cm²		143 MW/cm²	
532 nm, 7 ns, 10 Hz	0.6 J/cm²		86 MW/cm²	
266 nm, 7 ns, 10 Hz	0.3 J/cm²		43 MW/cm²	
PHYSICAL CHARACTERISTICS				
Effective Aperture	10 mm Ø			
Absorber (High Damage Threshold)	H5			
Dimensions	46H x 46W x 13D mm	46H x 46W x 21.4D mm	50H x 50W x 21.5D mm	50H x 50W x 30D mm
Weight (head only)	0.13 kg	0.14 kg	0.19 kg	0.13 kg
ORDERING INFORMATION				
Product Name	UP10P-2S-H5-L-D0	UPF10-2S-H5-L	UP10K-2S-H5-L-D0	UPF10K-2S-H5-L
Product Number (without stand)	202873	Call	202872	Call
 Add Extension for INTEGRA (USB)	-INT	-INT	-INT	-INT
Product Number (without stand)	203033	Call	203035	Call
 Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR	-IDR
Specifications are subject to change without notice // Compatible stand: P/N 200160				

* For the calibrated spectral range, see the user manual.

- a. Nominal value, actual value depends on electrical noise in the measurement system.
b. With anticipation.
c. Maximum output voltage = sensitivity x maximum power.
d. Including linearity with power.
e. For 360 µs pulses. Higher pulse energy possible when customized for long pulses (ms), less for short pulses (ns).
f. At 1064 nm, 10 W CW.