



XLP12

12 mm Ø, 0.5 μ W - 3 W – Low Power Thermopile



KEY FEATURES

- 1. LOW POWER THERMOPILE**
Noise level of a photo detector with the large bandwidth and high power capacity of a thermal device
- 2. MINIMAL THERMAL DRIFT**
Only 6 μ W/°C (with the IR filter)
- 3. HIGH SENSITIVITY**
200 mV/W (without the IR filter)
- 4. SPECIAL MODEL FOR ULTRASHORT PULSES**
VP (Volume Absorber) version is perfect for low power lasers with ultrashort pulses (ps and fs)
- 5. IR FILTER (XLPF12 MODEL)**
Removes unwanted IR interference
- 6. ISOLATION TUBE**
Eliminates power fluctuations created by air turbulence
- 7. SMART INTERFACE**
Containing all the calibration data
- 8. integra OPTIONS**
 - Standard: USB Output (-INT)
 - In Option: RS-232 Output (-IDR)

AVAILABLE MODELS



XLP12-3S-H2
(3W-Broadband)



XLPF12-3S-H2
(3W-Broadband-IR Filter)



XLP12-3S-VP
(3W-Volume Absorber)

ACCESSORIES



Stand with Steel Post
(Model Number: 200160)



Extension Cables
(4, 15, 20 or 25 m)



IR Filter
(Mounted)



Fiber Adaptors & Connectors
(FC, ST and SMA)



Pelican Carrying Case

SEE ALSO

HOW IT WORKS	14
CALIBRATION	6
TECHNICAL DRAWINGS	96
ABSORPTION CURVES	100
COMPATIBLE MONITORS	
MAESTRO	20
TUNER	24
UNO	26
S-LINK	28
P-LINK	30
M-LINK	32
LIST OF ALL ACCESSORIES	194

APPLICATION NOTE

MEASURING LASER POWER WITH A
THERMOPILE DETECTOR: THE BASICS! 202175

XLP12



SPECIFICATIONS

	XLP12-3S-H2	XLPF12-3S-H2	XLP12-3S-VP			
MAX AVERAGE POWER (CONTINUOUS / 1 MINUTE)	3 W / 3 W Broadband Absorber	3 W / 3 W Broadband Absorber, with IR Filter	3 W / 3 W Volume Absorber			
EFFECTIVE APERTURE	12 mm Ø	12 mm Ø	12 mm Ø			
COOLING METHOD	Convection	Convection	Convection			
MEASUREMENT CAPABILITY						
Spectral Range	0.19 – 20 µm *	0.28 – 2.1 µm ^a	0.25 – 20 µm *			
Noise Equivalent Power ^b	0.5 µW	0.5 µW	0.5 µW			
Thermal Drift ^c	12 µW/°C	6 µW/°C	12 µW/°C			
Rise Time (nominal) ^d	2.5 sec	2.5 sec	3 sec			
Sensitivity (typ into 100 kΩ load) ^e	200 mV/W	180 mV/W	220 mV/W			
Calibration Uncertainty ^f	±2.5 %	±2.5 %	±2.5 %			
Repeatability	±0.5 %	±0.5 %	±0.5 %			
Energy Mode						
Sensitivity	25 mV/J	22.5 mV/J	---			
Maximum Measurable Energy ^g	5 J	5 J	---			
Noise Equivalent Energy ^b	12 µJ	12 µJ	---			
Minimum Repetition Period	16 sec	16 sec	---			
Maximum Pulse Width	300 ms	300 ms	---			
Accuracy with energy calibration option	±5 %	±5 %	---			
DAMAGE THRESHOLDS						
Maximum Average Power Density ^h	1 kW/cm²	1 kW/cm²	30 W/cm² @ 1064 nm 8 W/cm² @ 532 nm 4 W/cm² @ 355 nm			
Pulsed Laser Damage Thresholds	Max Energy Dens.	Peak Power Dens.	Max Energy Dens.	Peak Power Dens.	Max Energy Dens.	Peak Power Dens.
1064 nm, 360 µs, 5 Hz	5 J/cm²	14 kW/cm²	5 J/cm²	14 kW/cm²	---	---
1064 nm, 7 ns, 10 Hz	1 J/cm²	143 MW/cm²	1 J/cm²	143 MW/cm²	4 J/cm²	571 MW/cm²
532 nm, 7 ns, 10 Hz	0.6 J/cm²	86 MW/cm²	0.6 J/cm²	86 MW/cm²	3 J/cm²	429 MW/cm²
355 nm, 7 ns, 10 Hz	---	---	---	---	1 J/cm²	143 MW/cm²
266 nm, 7 ns, 10 Hz	0,3 J/cm²	43 MW/cm²	0,3 J/cm²	43 MW/cm²	---	---
PHYSICAL CHARACTERISTICS						
Effective Aperture	12 mm Ø	12 mm Ø	12 mm Ø			
Absorber (High Damage Threshold)	H2	H2	VP (Volume Absorber)			
Dimensions	73H x 73W x 20D mm (72D mm with tube)	73H x 73W x 28D mm (80D mm with tube)	73H x 73W x 20D mm (72D mm with tube)			
Weight (head only)	0.31 kg	0.32 kg	0.32 kg			
ORDERING INFORMATION						
Product Name	XLP12-3S-H2-D0	XLPF12-3S-H2-D0	XLP12-3S-VP-D0			
Product Number (without stand)	201032	201077	202227			
 Add Extension for INTEGRA (USB)	-INT	-INT	-INT			
Product Number (without stand)	202609	202611	203031			
 Add Extension for INTEGRA (RS-232)	-IDR	-IDR	-IDR			

Specifications are subject to change without notice // Compatible stand: P/N 200160

* For the calibrated spectral range, see the user manual.

a. This spectral range refers to the calibration traceability.
For details, please contact us at: info@gentec-eo.com.

b. Nominal value, actual value depends on electrical noise in the measurement system.

c. With Gentec-EO MAESTRO.

d. With anticipation.

e. Maximum output voltage = sensitivity x maximum power.

f. Including linearity with power.

g. For 360 µs pulses. Higher pulse energy possible when customized for long pulses (ms), less for short pulses (ns).

h. At 1064 nm, 1 W CW.