



PO Box 31126
Dayton, OH 45437
Tel: 937.252.2989 Fax: 937.258.3937
E-mail: info@exciton.com
www.exciton.com

EXALITE 392A

Catalog No.: 03921

CAS No.: N/A

MW: 583

Appearance: White Crystalline solid

Lasing Wavelength

Max. (nm)	Range (nm)	Pump Source (nm)	Solvent	Concentration (molar)	Abs λ -max	Fl λ -max
--------------	---------------	---------------------	---------	--------------------------	-----------------------	----------------------

The Exalite dyes (Exalite 392A, Exalite 404, Exalite 411, Exalite 417 and Exalite 428) all have excellent operating lifetimes. The preferred solvent is p-Dioxane. Most of these dyes have very high absorption coefficients at 355nm, making them excellent candidates for pumping with the third harmonic of the Nd:YAG laser as well as under XeCl(308nm) pumping.

392	373-397	XeCl(308) ^{177b}	p-Dioxane	4.2×10^{-4}	331 ^c	368 ^c
389	382-396	Nd:YAG(355) ¹¹⁰	p-Dioxane	$\sim 6.5 \times 10^{-5}$		385
389	383-398	Nd:YAG(355) ⁵⁷	p-Dioxane	2.8×10^{-4} (osc), 0.8×10^{-4} (amp)		407(sh)

c = cyclohexane

REFERENCES:

57. Quanta-Ray, Note: Quanta-Ray is now incorporated as a part of Spectra-Physics, 1250 W. Middlefield Road, Mountain View, CA 94039
110. Lumonics Inc., 105 Schneider Road, Kanata, (Ottawa), Ontario, Canada K2K 1Y3
177. Exciton and Associates, unpublished data, 1987-1989; **a.** Characterization of New Excimer Pumped UV Laser Dyes I. p-Terphenyls, D.J. Schneider, D.A. Landis, P.A. Fleitz, C.J. Seliskar, J.M. Kauffman and R.N. Steppel, *Laser Chem.*, 11, 49 (1991); **b.** Characterization of New Excimer Pumped UV Laser Dyes 2. p-Quaterphenyls, P.A. Fleitz, C.J. Seliskar, R.N. Steppel, J.M. Kauffman, C.J. Kelley and A. Ghiorghis, *Laser Chem.*, 11, 99 (1991); **c.** Characterization of New Excimer Pumped UV Laser Dyes 3. p-Quinqu-, Sexi-, Octi- and Deciphenyls, C.J. Seliskar, D.A. Landis, J.M. Kauffman, M.A. Aziz, R.N. Steppel, C.J. Kelley, Y. Qin and A. Ghiorghis, *Laser Chem.*, 13(1), 19 (1993)